# TDS: (Technical Data Sheet)



## **GLOBAL MOLY-SPRAY:**

Dry film spray lubricant with Molybdenum Bisulphide intended for service temperatures up to 450° C.

### **DESCRIPTION AND APPLICATIONS:**

GLOBAL MOLY-SPRAY builds a long life lubricating dry film, completely homogeneous, adhesive, which resists high pressures and strong temperatures variations. Thus, it provides better sliding and reduces the friction coefficient.

GLOBAL MOLY-SPRAY is used for the lubrication of spindles, guides, screws, sliders, axles, bolts, and hardly reachable mechanisms.

GLOBAL MOLY-SPRAY avoids working residues and dust particles adhesion to the machines sliding surfaces, mainly in the textile industry. Therefore, GLOBAL MOLY-SPRAY is suitable lubricant for width adjust spindles in tensing stenter machines.

Colour; dark grey.

#### WAY TO USE:

- Prior to GLOBAL MOLY-SPRAY spraying, clean the metallic surfaces.
- Keep the can in vertical position, even when applying or storing.
- Apply the product from about 25-30 cm distance the part to be sprayed.
- After using hold the can upside down until the exhaust of pure gas, to avoid the plugging and drying of the spraying nozzle.

#### **CAUTIONS:**

- The normal ones when using lubricants packed in sprays.
- Protect the eyes and prevent inhalation of vapors.
- Don't smoke while using.
- Product under pressure, do not pinch or expose to fire, even when empty.
- Turn upside down and spray a couple of seconds to clean after use.
- MSDS as per European regulations is available.

#### PACKING:

520 ml total volume spray-can, packed in 12 unit's box.

The statements made in this publication are according to our present knowledge. They do not absolve the user from own examinations. A legally binding assurance of certain properties or suitability for a specific use cannot be derived from our statements. Possibly existing laws and regulations concerning the handling and use of our products have to be observed by the receiver of our products himself.